


# Alarm Siren AS-01

Suitable for indoor use.




## Technical Description

Voltage	12 - 24 VDC
Operating Temperature	-25 / +70 °C
Humidity Range	%10 - %93 (Non-Condensing)
Sound Level	80 dB

# Alarm Siren AS-01

## Siren Connection

- 1- Connect the power source's "+" (Red) cable to the siren's "+" socket.
- 2- Data collection of power source "-" (Black) terminal (DCT200) to the DO1 (Digital Output / Digital Output) socket.
- 3- Connect the siren's "-" socket with the COM socket to the right of the DO1 socket.



Any of the DO (Digital Output) ports can be used for siren connection.

\* In RetmonEMS application, you have to select the port (DO1 / DO2) where you are assembling for the siren under "Settings> Equipment> Siren On"